

Working with Bihl+Wiedemann

General process for working with Bihl+Wiedemann products

1. Select products

Personal consultation is our highest priority. We look forward to telephone or email contact. You will be then be connect-ed directly to your personal contact person.

General contact data for Bihl+Wiedemann

Bihl+Wiedemann GmbH
 Floßwörthstraße 41
 68199 Mannheim

Phone: +49 621 33996-0

Fax: +49 621 3392239

E-Mail: mail@bihl-wiedemann.de

Web: www.bihl-wiedemann.de

The product selectors on the Bihl+Wiedemann website help you in choosing the products. Select the criteria that are im-portant for you to narrow down the list of products.


Gateways

10 of 75 products selected


Type	Model	Fieldbus interface	Number of AS-i networks, number of AS-i Master	1 power supply, 1 gateway for 2 AS-i networks, inexpensive power supplies	Diagnostic and configuration Interface	Recognition of duplicate AS-i addresses
PROFIsafe, PROFIBUS	Gateway	EtherCAT	1 AS-i network, 1 AS-i Master	no, max. 8 A/AS-i-network	Ethernet-diagnostic	no
PROFIsafe, PROFINET	Gateway with integrated Safety Monitor	EtherNet/IP + Modbus/TCP	2 AS-i networks, 1 AS-i Master	no, max. 8 A/AS-i network, redundant supply	Ethernet-fieldbus	yes
RS-232-AS-i		Modbus/RTU; RS-485	2 AS-i networks, 2 AS-i Masters	yes, max. 4 A/AS-i network	Ethernet fieldbus + Ethernet diagnostic	
RS-485-Modbus-AS-i		POWERLINK			Ethernet fieldbus + RS 232	
Safety; CANopen		PROFIBUS			RS-232	
Safety; CC-Link		PROFINET				
Safety; EtherCAT		RS-232				
Safety; EtherNet/IP + Modbus/TCP		Sercos				
Safety; POWERLINK		complete.set.CompactLogix; MicroLogix1500				
Safety; PROFIBUS		complete.set.ControlLogix				
Safety; PROFINET						

Figure	Type	Model	Protection rating	Fieldbus interface	Number of AS-i networks, number of AS-i Master	1 power supply, 1 gateway for 2 AS-i networks, inexpensive power supplies	Diagnostic and configuration interface	Recognition of duplicate AS-i addresses	AS-i fault detector	Programming in C	Inputs digital, EDM	Inputs Safety, SIL 3, Cat. 4	Imp exp
BWU2828	Safety, PROFINET	Gateway with integrated Safety Monitor	IP20	PROFINET	2 AS-i networks, 2 AS-i Masters	yes, max. 4 A/AS-i network	Ethernet fieldbus + Ethernet diagnostic	yes	yes	optional	6	3 x 2 channels	ma cha 192 cor
BWU2642	Safety, PROFINET	Gateway with integrated Safety Monitor	IP20	PROFINET	2 AS-i networks, 2 AS-i Masters	yes, max. 4 A/AS-i network	Ethernet fieldbus + RS 232	yes	yes	optional	4	-	ma cha 192 cor
BWU3080	Safety, PROFINET	Gateway with integrated Safety Monitor	IP20	PROFINET	2 AS-i networks, 2 AS-i Masters	no, max. 8 A/AS-i network, redundant supply	Ethernet fieldbus + Ethernet diagnostic	yes	yes	optional	6	3 x 2 channels	ma cha 192 cor

The Info fields in the column header help you with the individual criteria.



The Detail view provides additional information about the products.



2. Purchase products

Get in touch with your personal contact person. For projects involving many components we will create an offer custom tailored to your needs.


To order replacement parts or individual components, the simplest and fastest way is via email or through the Webshop.

3. Insert products into your plan

Register on our website. This gives you access to the download area. On the “Download” tab in the product detail view you will find all the important documents. For planning you will need:

- Data sheet
- CAD data
- Eplan macro
- Installation instructions

If you are using safety products, we recommend creating the hardware configuration in the ASIMON360 safety software already in the planning stage. ASIMON360 automatically assigns the AS-i addresses and displays them in an organized view. This makes planning of the AS-i network and address assignment significantly easier.



4. Place the products in operation

4.1 Electrical connection

Electrical connections are described in the installation guide which is included with the products in printed form as well. There you will also find various wiring examples.

4.2 Create the PLC program

Download the device description file for your AS-i gateway from the website and insert the desired data modules. The compact manual, which you will also find in the Download area, describes the most important data modules and gives you recommendations for diagnostics.

We offer example programs for some controllers which contain a simple basic configuration for cyclical data exchange and diagnostics. All the example projects are found here:

<http://www.bihl-wiedemann.de/en/support/downloads/application-examples.html>

4.3 Startup without safety products

To commission an AS-i network without safety you need no software. The AS-i master is configured bottom-up simply using the display menu and buttons.

- Use a handheld AS-i address programming device or use the display menu of the AS-i master to address the slaves
- Connect all slaves
- Save the configuration in the AS-i master using the Quick Setup function in the display menu of the AS-i master.

4.4 Startup with safety products

After you have created the complete safety configuration using ASIMON360, use the ASIMON360 Startup Wizard to place the complete AS-i network in operation.

4.5 Check installation

Use our software for diagnostics, service and release measurements. The software is available in the package (BW2916) or separately (BW2902). After starting, the software automatically creates a log which you can include with the documentation and give to the operator when the system is handed over. This involves running the system for a period of time (for example 20 minutes) during which all the situations and conditions are present. The software runs the entire time and thereby provides a qualitative assessment of the installation.

5. How to get help

- o Get in touch with us:

Technical support and contact

- o You can reach our Technical Support at:
Phone: +49 621 33996-0 and Fax: +49 621 3392239

Telephone contact for your issues

For special questions and inquiries you can reach us at the following telephone numbers:

- o Inside Sales: Offers / Pricing
+49 621 33996-940
- o Purchasing
+49 621 33996-950
- o Order Processing: Orders / Order confirmations
+49 621 33996-980
- o Main desk
+49 621 33996-0

Email contact for your issues

For specific issues you can reach us at the following email addresses:

- o For offer-related questions
offer@bihl-wiedemann.de
- o For questions about your order and delivery times
order@bihl-wiedemann.de
- o For technical questions
asiexpert@bihl-wiedemann.de
- o For interest in working at Bihl+Wiedemann
bewerbung@bihl-wiedemann.de
- o For general questions of all kinds
mail@bihl-wiedemann.de

Help and self-help

The software for diagnostics, service and release measurement (BW2902) is helpful even for technical problems. It checks, reports errors and gives you helpful tips for fixing errors. It is also possible to send a detailed log to Bihl+Wiedemann Support. Our experts can use this log to assist you efficiently should it become necessary.